



ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSR-100-B	BODY	ALUMINUM	1
2	SRB-104	BUSHING	NEOPRENE	1
3	RSR-100-ND	NUT	ALUMINUM	1
4	R-104-D	MESH	STAINLESS WIRE	1
5	LN-50	LOCKNUT	ADD: L, C.R.S. ZINC PLATED	1



CATALOG NUMBER	SEALING RANGE	BODY BORE
RSR-104-E	.188 - .250	.610

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	<b>REMKE</b> <b>REMKE INDUSTRIES</b> 310 CHADDICK DR, WHEELING, IL. 60090	
A	6/24/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL $\pm 1/64$ ANGULAR: MACH $\pm 1^\circ$ BEND $\pm 1^\circ$ ONE PLACE DECIMAL $\pm .015$ TWO PLACE DECIMAL $\pm .010$ THREE PLACE DECIMAL $\pm .005$	DRAWN	JCN	6/13	TITLE: RSR-104-E SERIES
			INTERPRET GEOMETRIC TOLERANCING PER:	CHECKED			SIZE <b>A</b> DWG. NO. RSR-104-E ASSEMBLY
			MATERIAL <b>ALUMINUM</b>	ENG APPR.			
			FINISH	MFG APPR.			SCALE: 1:1 SHEET 1 OF 1
			DO NOT SCALE DRAWING	Q.A.			

5

4

3

2

1