



PART NUMBER	SEALING RANGE	BODY BORE
RSR-300	NO HOLES	.990
RSR-304	.188 - .250	.990
RSR-305	.250 - .312	.990
RSR-306	.312 - .375	.990
RSR-307	.375 - .437	.990
RSR-308	.438 - .500	.990
RSR-309	.500 - .562	.990
RSR-310	.562 - .625	.990
RSR-311	.562 - .688	.990
RSR-312	.625 - .750	.990
RSR-313	.688 - .812	.990
RSR-314	.750 - .875	.990
RSR-315	.812 - .938	.990
RSR-316	.875 - 1.000	.990

ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY.
1	RSR-300-B	BODY	ALUMINUM	1
2	SRB-300	BUSHING	NEOPRENE	1
3	SW-300	WASHER	C.R.S. ZINC PLATED	1
4	RSR-300-N	NUT	ALUMINUM	1
5	LN-100	LOCK NUT	ADD: L, C.R.S. ZINC PLATED	1

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	REMKE REMKE INDUSTRIES 310 CHADDICK DR, WHEELING, IL. 60090	
A	4/22/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL $\pm 1/64$ ANGULAR: MACH $\pm 1^\circ$ BEND $\pm 1^\circ$ ONE PLACE DECIMAL $\pm .015$ TWO PLACE DECIMAL $\pm .010$ THREE PLACE DECIMAL $\pm .005$	DRAWN	JCN	4/13	TITLE: RSR-300 SERIES
			INTERPRET GEOMETRIC TOLERANCING PER:	CHECKED			
			MATERIAL	ENG APPR.			
			ALUMINUM	MFG APPR.			
			FINISH	Q.A.			
			DO NOT SCALE DRAWING	PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF REMKE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF REMKE INDUSTRIES IS PROHIBITED.		SIZE A	DWG. NO. RSR-300 ASSEMBLY
				SCALE: 3:2			SHEET 1 OF 1