



ITEM NO.	PART NUMBER	DESCRIPTION	MATERIAL	QTY
1	RSR-1000-B	BODY	ALUMINUM	1
2	SRB-003 - SRB-007	BUSHING	NEOPRENE	1
3	SW-000	WASHER	C.R.S. ZINC PLATED	1
4	RSR-000-N	NUT	ALUMINUM	1
5	LN-50	LOCK NUT	ADD: L, C.R.S. ZINC PLATED	1

PART NUMBER	SEALING RANGE	BODY BORE
RSR-1003	.125 - .188	.470
RSR-1004	.188 - .250	.470
RSR-1005	.250 - .312	.470
RSR-1006	.312 - .375	.470
RSR-1007	.375 - .438	.470

REV.	DATE	CHANGE	UNLESS OTHERWISE SPECIFIED:	NAME	DATE	REMKE REMKE INDUSTRIES 310 CHADDICK DR, WHEELING, IL. 60090	
A	04/22/13	DRAWING RELEASED	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ± 1° BEND ± 1° ONE PLACE DECIMAL ± .015 TWO PLACE DECIMAL ± .010 THREE PLACE DECIMAL ± .005	JCN	4/13	TITLE: RSR-1000 SERIES	
			INTERPRET GEOMETRIC TOLERANCING PER:			SIZE DWG. NO. A RSR-1000 ASSEMBLY	
			MATERIAL ALUMINUM	PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF REMKE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF REMKE INDUSTRIES IS PROHIBITED.		SCALE: 3:1	
			FINISH			SHEET 1 OF 1	
			DO NOT SCALE DRAWING				

5

4

3

2

1