



BCS-NX5210

PROFIBUS-DP slave

Redundant Profibus DP slave module
 Hot-Swap of I/O modules
 Automatic baud rate detection
 Ability to use up to 20 I/O modules in a single rack
 Local advanced diagnostic service

Facts

General description

Article number	66.014.927-2
Warranty	2 year

Mechanical

Certificates	CE, ROHS, UL, DNV
Module dimensions (W x H x D)	36.00 x 114.63 x 115.30 mm
Net weight	200 g

System

Hot Swap	Yes
One Touch Diag (OTD)	Yes
Status and diagnostics indication	Yes
Transmission rate	9.6 to 12.000 kbit/s
Redundancy support	Yes
Application layer	Profibus DP V0
Cable type	Profibus DP cable
Maximum cable length	According to the Profibus DP standard