



### Main

|                                    |  |
|------------------------------------|--|
| Range                              | Spacial  |
| Product or Component Type          | Cable gland plate  |
| Accessory / separate part category | Cable management accessory   |
| Anwendung                          | Multi-purpose  |
| Range compatibility                | Spacial SF   |
| Mounting Location                  | Enclosure bottom   |
| Cable gland type                   | Standard   |
| Cable entry                        | 1 entry  |
| Device composition                 | Fixing elements<br>1 plate<br>Self extinguishing polyurethane adhesive gasket with cross-section of 15 x 25 mm |
| Quantity per Set                   | Set of 1   |
| Material                           | Galvanised steel   |

### Complementary

|           |  |
|-----------|--|
| Height    | 1.18 in (30 mm)  |
| Width     | Nominal 39.37 in (1000 mm)<br>Useful 32.13 in (816 mm)<br>Real 33.46 in (850 mm) |
| Depth     | Nominal 23.62 in (600 mm)  |
| Thickness | 0.06 in (1.5 mm)   |

### Ordering and shipping details

|                       |                                     |
|-----------------------|-------------------------------------|
| Category              | 80036-ENCLOSURE SYSTEMS ACCESSORIES |
| Discount Schedule     | ES1                                 |
| GTIN                  | 3606485126340                       |
| Nbr. of units in pkg. | 1                                   |
| Package weight(Lbs)   | 13.19 lb(US) (5.983 kg)             |
| Returnability         | No                                  |
| Country of origin     | FR                                  |

### Packing Units

|                        |                    |
|------------------------|--------------------|
| Unit Type of Package 1 | PCE                |
| Package 1 Height       | 1.18 in (3.0 cm)   |
| Package 1 width        | 13.78 in (35.0 cm) |
| Package 1 Length       | 33.46 in (85.0 cm) |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Green Premium product   |
| RECh Regulation          | RECh Declaration  |
| RECh free of SVHC        | Yes   |
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Mercury free             | Yes   |

---

|                            |   |
|----------------------------|---|
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |

---

### Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---