

### Main

Range	PowerLogic
Product or Component Type	Current transformer
Analogue Output Type	Voltage output
Electrical connection	Plug-in 30 ft (9.14 m) AWG 18) 600 V
Line Rated Current	75 A

### Complementary

Current transformer type	Split core
--------------------------	------------

### Environment

Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
---------------------------------------	----------------------------





### Ordering and shipping details

Category	09795-POWERLOGIC CURRENT TRANSFORMERS
Discount Schedule	PL1
GTIN	3606481985453
Nbr. of units in pkg.	1
Package weight(Lbs)	17.64 oz (500.0 g)
Returnability	No
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.02 in (22.9 cm)
Package 1 width	9.02 in (22.9 cm)
Package 1 Length	14.02 in (35.6 cm)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>