



Main

Range	Spacial
Accessory / separate part category	Interface accessory
Product or Component Type	Box keyboard
Anwendung	Multi-purpose
Nennmaße des Gehäuses	-
Mounting Location	Control enclosure
Range compatibility	Spacial S3CM
Device composition	Fixing elements 1 box 2 bracket 1 trim rail 1 hose for cable entry
Quantity per Set	Set of 1

Complementary

Material	Body steel Front face and trim frame aluminium
Color	Body Gray RAL 7035 Front face and trim frame Gray RAL 7040)
Surface Finish	Epoxy-polyester powder
Fixing mode	By fixing element - on control enclosure
Operating angle	120 °
Height	External 9.84 in (250 mm) Real 11.26 in (286 mm)
Width	External 23.62 in (600 mm) Real 27.44 in (697 mm)
Depth	External 4.33 in (110 mm) Real 4.92 in (125 mm)

Environment

IP degree of protection	IP54
IK degree of protection	IK10
Net Weight	18.91 lb(US) (8.578 kg)

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480213205
Nbr. of units in pkg.	1
Package weight(Lbs)	18.91 lb(US) (8.578 kg)
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	24.41 in (62 cm)
Package 1 width	16.54 in (42 cm)
Package 1 Length	6.69 in (17 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------