

Product data sheet

Characteristics

HCJ3291WP

Box, I-Line Panelboard, HCJ, 33.14in W x 91in H x 11.75in D, Type 1/3R, w/front



Main

Range of Product	I-Line
Product or Component Type	Enclosure
Device Application	Panelboard

Complementary

Line Rated Current	800 A
Cover type	Lockable cover
Mounting Mode	Wall mount
Net Weight	338 lb(US) (153.31 kg)
Height	91 in (2311.40 mm)
Depth	11.75 in (298.45 mm)

Environment

NEMA Degree of Protection	NEMA 1 NEMA 3R
Standards	UL CSA

Ordering and shipping details

Category	00110-RTA PANELBOARD BOXES - SPECIAL, 3R, ETC.
Discount Schedule	PE1A
GTIN	785901492788
Nbr. of units in pkg.	1
Package weight(Lbs)	338.00 lb(US) (153.314 kg)
Returnability	Yes

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	90.98 in (231.1 cm)
Package 1 width	32.01 in (81.3 cm)
Package 1 Length	11.73 in (29.8 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------