

Main

| | |
|---------------------------|---------------------------------------|
| Range | PowerLogic |
| Product or Component Type | Current transformer |
| Analogue Output Type | Voltage output |
| Electrical connection | Plug-in 60 ft (18.29 m) AWG 18) 600 V |
| Line Rated Current | 75 A |

Complementary

| | |
|--------------------------|------------|
| Current transformer type | Split core |
|--------------------------|------------|

Environment

| | |
|---------------------------------------|----------------------------|
| Ambient Air Temperature for Operation | -40...131 °F (-40...55 °C) |
|---------------------------------------|----------------------------|

Ordering and shipping details

| | |
|-----------------------|---------------------------------------|
| Category | 09795-POWERLOGIC CURRENT TRANSFORMERS |
| Discount Schedule | PL1 |
| GTIN | 3606481985460 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 35.27 oz (1000.0 g) |
| Returnability | No |
| Country of origin | CN |

Packing Units

| | |
|------------------------|--------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 9.02 in (22.9 cm) |
| Package 1 width | 9.02 in (22.9 cm) |
| Package 1 Length | 14.02 in (35.6 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |