



Main

Range of Product	Harmony XK
Product or Component Type	Complete joystick controller
Device short name	XDP
Mounting diameter	1.89 in (48 mm)
Bezel material	Plastic
Sale per indivisible quantity	1

Complementary

Operator position information	2 positions
Operator direction information	1 direction
Contacts type and composition	8 NO
Contacts usage	Standard
Mechanical durability	1000000 cycles
Return	Spring return
Height	6.24 in (158.6 mm)
Width	2.56 in (65 mm)
Depth	1.73 in (44 mm)
Net Weight	1.10 lb(US) (0.5 kg)

Environment

Standards	EN/IEC 60947-5-5 EN/IEC 60947-5-4 JIS C 4520 UL 508 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-1
Ambient Air Temperature for Operation	-40...140 °F (-40...60 °C)
IP degree of protection	IP65

Ordering and shipping details

Category	22476-JOYSTICKS (NOT CRANE)
Discount Schedule	I
GTIN	785901320746
Nbr. of units in pkg.	1
Package weight(Lbs)	17.28 oz (489.88 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.00 in (7.62 cm)
Package 1 width	3.50 in (8.89 cm)
Package 1 Length	7.00 in (17.78 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------