

Main

Range	PowerLogic
Product or Component Type	Current transformer
Analogue Output Type	Voltage output
Electrical connection	Plug-in 12 ft (3.66 m) AWG 18) 600 V
Line Rated Current	75 A

Complementary

Current transformer type	Split core
--------------------------	------------

Environment

Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
---------------------------------------	----------------------------





Ordering and shipping details

Category	09795-POWERLOGIC CURRENT TRANSFORMERS
Discount Schedule	PL1
GTIN	3606481985446
Nbr. of units in pkg.	1
Package weight(Lbs)	14.11 oz (400.0 g)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.99 in (20.3 cm)
Package 1 width	7.99 in (20.3 cm)
Package 1 Length	7.99 in (20.3 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration