

USB-A to RJ45 Rollover Console Cable (M/M) - Cisco Compatible, 250 Kbps, 6 ft. (1.83 m), Black

MODEL NUMBER: U009-006-RJ45-X











Rollover console cable connects your computer or laptop's USB-A port to a serial-based Cisco device with a console port.

Features

Ideal for IT Pros Who Need a Connection Between Computer and Cisco Console Device This rollover cable is designed for consumers or IT professionals who want a reliable connection between their computer or laptop's USB-A port and a Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port. The cable works with both older and new Cisco models, supporting data transfer rates up to 250 Kbps.

Top-Quality Construction for Top-of-the-Line PerformanceNo extra software or external power is required to use this 6-ft. (1.83 m) cable. Premium double shielding eliminates crosstalk and reduce EMI/RFI line noise that can disturb your electronics and inflict hardware damage or data loss. The U009-006-RJ45-X is compatible with Windows (up to 11), Mac (up to 10.12) and Linux (up to Redhat 9.0) operating systems.

Highlights

- Great for programming, resetting or rebooting a Cisco switch, firewall, router or modem
- 6-ft. (1.83 m) cable supports data transfer speeds up to 250 Kbps
- Double-shielded construction cuts crosstalk and EMI/RFI line noise
- Plug-and-play operation with no software required for easy, immediate installation
- Compatible with Windows, Mac and Linux

Applications

 Program, reset or reboot a serial-based Cisco switch, firewall, router or modem through its console port

System Requirements

- Computer or laptop with USB-A port
- Serial-based Cisco device with console port
- Windows (up to 11), Mac (up to 10.12), or Linux (up to Redhat 9.0) operating systems

Package Includes

 U009-006-RJ45-X USB to RJ45 Rollover Console Cable (M/M), Black, 6-ft. (1.83 m)

Specifications

OVERVIEW	
UPC Code	037332222107
Technology	Cat5/5e; USB
Host Connector	USB A (MALE)
POWER	
USB Power Delivery (PD) Charging Support	No
PHYSICAL	



Black	
PVC, PE	
Black	
PVC	
5.5mm; 4.7mm +/- 0.15	
26	
6	
1.83	
72	
183	
Polybag	
0.1984	
0.09	
ENVIRONMENTAL	
32° to 104°F (0° to 40°C)	
-4° to 140°F (-20° to 60°C)	
0% to 90% RH (Non-Condensing)	
CONNECTIONS	
USB A (MALE)	
RJ45 (MALE)	
FEATURES & SPECIFICATIONS	
USB 1.1 (up to 12 Mbps)	
No	
No	
Yes	
STANDARDS & COMPLIANCE	
RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT	
3-year limited warranty	







© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.