

## 48-Device AC Mobile Charging Cart - Laptops and Chromebooks, 120V, NEMA 5-15P, 10 ft. (3.05 m) Cord, Black

MODEL NUMBER: CSC48AC



Charges, secures and organizes up to 48 Chromebooks and laptops in education, healthcare, retail, warehouse and office environments.

### Features

**Mobile Charging Cart Accommodates up to 48 Chromebooks and Laptops**This 120V charging cart provides timed AC charging, secure storage and cord management for as many as 48 Chromebooks and laptops. The connected devices' AC adapters plug into 48 NEMA 5-15R outlets, which provide up to 1,440 watts for charging. A built-in circuit breaker protects the devices against overloads.

**High-Speed Zone Charging Conserves Energy and Helps Avoid Potential Overloads**The 48 NEMA 5-15R outlets are split evenly into two color-coded charging zones to support more devices and higher wattages without overloads. A built-in timer alternates charging zones every hour. LEDs indicate which zone is being charged at any given time.

**Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure**Constructed from heavy-duty steel covered with a black powder-coated finish, this laptop charging cart provides safe, secure storage. Devices and their power adapters are stored in separate compartments. The front and back doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the front door can be fastened with a user-supplied padlock. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

**Moving Your Devices from Room to Room Is Easy**Large swivel casters with non-marking wheels improve the ride over uneven surfaces and lock to help prevent unwanted movement. The reversible wide-grip handle makes the cart easy to control. Corner safety bumpers protect walls and doorways from scratches. The compact Chromebook charging cart takes up about the same amount of physical space as a typical A/V cart.

**Well-Organized to Avoid Confusing Cable Clutter**Heavy power adapters store out of the way in removable baskets. Cables and connectors run through zoned slots and an overhead cable manager, keeping them organized and out of the way. Adjustable dividers accommodate up to 16 devices per shelf, and device spaces are numbered for easy identification. A power cord wrap keeps the input cord out of the way when moving the charging station. The 10-ft. (3.05 m) cord with space-saving right-angle NEMA 5-15P plug allows great flexibility in reaching AC outlets.

### Highlights

- 48 internal NEMA 5-15R outlets provide up to 1,440 total watts for charging
- Hourly timer alternates charging zones to help prevent overloads
- In-cabinet RJ45 jack connects Ethernet peripherals, including routers and hotspots
- Dual external NEMA 5-15R outlets provide power for a monitor or projector
- 10-ft. (3.05 m) cord with NEMA 5-15P plug allows great flexibility in reaching AC outlets

### Applications

- Charge up to 48 Chromebooks and laptops in schools, businesses and government organizations that rely on the daily use of mobile devices
- Easily and safely transport connected devices from room to room
- Use the laminate top as a workstation or a sturdy platform for A/V equipment

### Package Includes

- CSC48AC 48-Device AC Charging Station Cart, Black
- Cart handle
- Input cord wrap
- (6) Protective bumpers
- (10) Hex screws
- Hex key
- (2) Keys
- Owner's manual

**Laminated Wood-Grain Top Doubles as a Convenient Workstation**The laminated top acts as a smooth writing surface and holds a projector, monitor or other peripherals that plug into two external NEMA 5-15R outlets controlled by an inside on/off switch. A pass-through RJ45 jack is provided for connecting Ethernet devices, such as a wireless router or hotspot, inside the cabinet.

## Specifications

OVERVIEW	
UPC Code	037332226075
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Functions	Charge; Secure
Device Compatibility	Chromebook; Laptop
Device Slots	48
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	48
Charging Method	AC
Charging Port Type	NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(48) 12A
Overcharge Protection	No
Charging Amps per Port	12A
PHYSICAL	
Color	Black
Material of Construction	Steel
Charging Station Form Factor	Mobile Cart
Shipping Dimensions (hwd / in.)	46.85 x 26.77 x 29.13
Shipping Weight (kg)	92.99

Slot Dimensions - Bottom (hwd / in.)	10.11 x 1.05 x 15.58
Slot Dimensions - Bottom (hwd / mm)	256.9 x 26.79 x 395.72
Slot Dimensions - Middle (hwd / in.)	10.13 x 1.05 x 15.58
Slot Dimensions - Middle (hwd / mm)	257.3 x 26.79 x 395.72
Slot Dimensions - Top (hwd / in.)	10.13 x 1.05 x 15.58
Slot Dimensions - Top (hwd / mm)	257.3 x 26.79 x 395.72
Unit Dimensions (hwd / in.)	43.050 x 26.040 x 28.840
Unit Dimensions (hwd / cm)	109.35 x 66.14 x 73.25 (con la manija instalada)
Unit Weight (lbs.)	147.82
Unit Weight (kg)	67.05
Number of Shelves	3
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	No
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 60950-1 (Canada); NOM (Mexico); UL 60950-1
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	Yes



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.