

# High-Speed HDMI Cable with Ethernet (M/M) - 4K, No Signal Booster Needed, Black, 45 ft.

## MODEL NUMBER: P568-045-HD





High-speed 4K cable connects audio/video components to an HDTV or monitor in your home theater or digital signage application.

### **Features**

**4K HDMI Cable Connects Home Theater or Digital Signage Audio/Video Components**This high-speed HDMI cable securely connects HDMI-enabled Chromebooks, MacBooks, tablets, PCs, Blu-ray players, game consoles, Roku/Apple TV boxes or satellite/cable TV receivers to HDTVs, HD monitors, projectors or home theater receivers. It allows you to extend your HDMI signal as far as 45 feet (13.7 meters) from the source without connecting a signal booster or having to use more expensive active optical cable (AOC) or Cat5/6 cable. It also supports Ethernet, so no separate cable is needed to connect devices online.

**Enjoy the Clarity of 4K HDMI Video with Multi-Channel Audio**This Tripp Lite 4K HDMI cable provides a pure digital connection that supports Ultra HD video resolutions up to 4K for crystal-clear picture and sound.

**Invest in Quality Construction for Reliable Performance**High-quality materials ensure outstanding performance throughout the 24 AWG cable's lifetime. Contacts and connectors are gold-plated to resist corrosion. Double shielding reduces line noise (EMI/RFI) that can disrupt signals traveling through the HDMI cord. When used with an Apple digital A/V adapter, the cable supports iPad2 video mirroring for playing games, watching videos or displaying presentations.

**45 ft. Cable Lets You Design an Audio/Video Application to Your Specifications**This long HDMI cable allows you greater flexibility in placing your home theater or digital signage components. For instance, your Blu-ray player or media server may be concealed some distance from the connected display for security purposes.

# Specifications

OVERVIEW	
UPC Code	037332252807

### **Highlights**

- 45 ft. length allows great flexibility in placing home theater or digital signage devices
- Supports UHD resolutions up to 4K for crystal-clear video
- Gold-plated connectors and contacts enable maximum conductivity and minimum data loss
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Plug-and-play operation with no booster required for easy, immediate installation

### **Applications**

- Watch 4K video from a Blu-ray player, game console, laptop or tablet on an Ultra HD television, monitor or projector
- Connect a Chromebook or MacBook to a conference table's A/V box to give a video presentation on a large screen
- Play online or PC video games that display optimal graphics
- Combine with an Apple digital A/V adapter to support iPad2 video mirroring
- Send 4K video content to digital signs or point-of-sale displays

### Package Includes

P568-045-HD High-Speed HDMI Cable, M/M, Black, 45 ft.



Product Type	Passive Cable	
Technology	HDMI	
Cable Type	Passive	
VIDEO		
Max Supported Video Resolution	3840 x 2160 (4K) @ 30Hz	
Max Supported Color Depth	24-bit True Color	
HDR Support	No	
3D Video Supported	Yes	
Chroma Sub Sampling	4:4:4	
EDID Support	Yes	
Signal Transmission	Bidirectional	
AUDIO		
Audio Specification	Stereo Audio	
INPUT		
Product Length (in.)	540	
Product Length (ft.)	45	
USER INTERFACE, ALERTS & COM	ITROLS	
LED Indicators	0	
PHYSICAL		
Color	Black	
Material of Construction	PVC	
Cable Jacket Color	Black	
Connector Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	10.0 mm	
Wire Gauge (AWG)	24	
Cable Length (ft.)	45	
Cable Length (m)	13.72	
Cable Length (in.)	540	
Ferrite Core	No	
Minimum Bend Radius	100mm	



Shipping Dimensions (hwd / in.)	13.80 x 11.00 x 0.50		
Shipping Weight (kg)	1.49		
ENVIRONMENTAL	ENVIRONMENTAL		
Operating Temperature Range	32° to 113°F (0° to 45°C)		
Storage Temperature Range	-40° to 176°F (-40° to 80°C)		
Relative Humidity	5% to 90%, Non-Condensing		
Operating Humidity Range	10% to 85% RH, Non-Condensing		
Storage Humidity Range	5% to 90% RH, Non-Condensing		
COMMUNICATIONS			
Consumer Electronics Control (CEC) Supported	Yes		
CONNECTIONS			
Side A - Connector 1	HDMI (MALE)		
Side B - Connector 1	HDMI (MALE)		
Connector Plating	Gold		
Contact Plating	Gold		
Connector Style	Straight		
Latching or Gripping Connector	No		
FEATURES & SPECIFICATIONS			
EMI/RFI Line Noise Protection	No		
Integrated/Removable Cable	No		
MST Support	No		
Antibacterial	No		
IP68 Rated	No		
IP20 Rated	No		
Fully Molded Connector Ends	No		
Ohms	No		
Integral Strain Relief	No		
Impedance-Matched Twisted-Pair Construction	No		
Scaler Function	No		
IP67 Rated	No		
Armored Cable	No		
Ethernet Support	Yes		



HDCP Specification	1.4	
DIN Mountable	No No	
STANDARDS & COMPLIANCE		
Product Certifications	IEC/EN 62040	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.