

## Safe-IT UV Locking Storage Cart for Mobile Devices and AV Equipment, Black

MODEL NUMBER: CSCSTORAGE2UVC



Locking cart on rolling casters offers UV-sanitized storage for tablets, cables and other mobile devices.

### Features

#### Secure Storage Cart Provides Ample Space for Laptops, Tablets and Cables

Constructed from heavy-duty steel with a black powder-coated finish, this Safe-IT™ locking cart provides safe, secure storage for your laptops, tablets and other valuable electronics. The front and back doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the doors can be fastened with user-supplied padlocks. Flow-through vents on the doors and side panels help protect the devices against overheating, and the specially coated shelves help prevent device scratches and scuffs.

#### UV Light Helps Sanitize Devices without Potentially Dangerous Heat, Liquids or Chemicals

The CSCSTORAGE2UVC helps reduce the presence of germs on your laptops, Chromebooks, tablets and AV equipment. Built-in ultraviolet lights help disinfect devices at the touch of a button by destroying most microbes without the use of damaging heat, liquids or chemicals. The germicidal UVC bulbs are on a timer to control the amount of UV exposure the devices receive. An LED on the exterior of the cabinet indicates when the doors are closed and the start button can be pressed to activate the 10-minute timer. A second LED indicates when the UVC lights are on. If a door is opened during sanitization, the lights automatically shut off for safety.

#### Moving Your Devices from Room to Room Is Easy

Large swivel casters with non-marking wheels improve the ride over uneven surfaces, including carpeting and thresholds, and lock to help prevent unwanted movement. The reversible wide-grip handle makes the cart easy to control. Corner safety bumpers protect walls and doorways from scratches. The compact cart takes up about the same amount of physical space, or even less, as a typical A/V cart.

#### Comes Ready for Immediate Use Right from the Box

The CSCSTORAGE2UVC ships fully assembled for instant deployment in schools, healthcare settings, corporate offices, warehouses, restaurants, hotels, retail stores, senior living facilities and other settings that rely on the daily use of mobile devices. The storage cart is powered by a 10-foot cord and NEMA 5-15P plug that connects to a compatible AC outlet.

## Specifications

### Highlights

- Steel enclosure locks with included keys to discourage theft, damage and tampering
- Ultraviolet (UVC) lights help disinfect devices without use of damaging heat or chemicals
- Vented side panels and doors allow flow-through ventilation to prevent overheating
- 10 ft. cord with NEMA 5-15P plug allows great flexibility in reaching AC outlets

### Package Includes

- CSCSTORAGE2UVC UV Locking Storage Cart
- Reversible handle
- (2) Protective bumpers
- (12) Hex screws
- Hex key
- (2) Keys
- Owner's manual

<b>OVERVIEW</b>	
UPC Code	037332266064
Product Type	Storage Cart
Device Compatibility	Amazon Kindle; Chromebook; Computer; DVR; Headphones; Laptop; Monitor/HDTV; Network Switch; Patch Panel; Phone; Projector; Server; Tablet; UPS; Watch
Device Slots	3
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	120
Input Frequency	60
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
Rack Height	0U
Rack Depth	Mid; Shallow
Maximum Device Depth (cm)	48.26
Maximum Device Depth (in.)	19
Maximum Device Depth (mm)	483
Shipping Dimensions (hwd / in.)	42.32 x 22.83 x 33.66
Shipping Dimensions (hwd / cm)	107.49 x 57.99 x 85.50
Shipping Weight (lbs.)	175.27
Shipping Weight (kg)	79.50
Slot Dimensions (hwd / in.)	16.00 x 30.33 x 20.00
Unit Dimensions (hwd / in.)	36.680 x 20.200 x 30.330
Unit Weight (lbs.)	138.890
Unit Weight (kg)	63.00
Weight Capacity - Stationary (kg)	113
Weight Capacity - Stationary (lbs.)	250
Number of Shelves	2
<b>FEATURES &amp; SPECIFICATIONS</b>	

Grounding Details	No
Antimicrobial	No
Built-In Circuit Breaker	No
Cord Management	Yes
Overcurrent Protection	No
EMI/RFI Line Noise Protection	No
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	Yes
Built-in Cable Management	No
Extra Wide	No
Locking	Yes
Lock Type	Key
Pre-Installed Casters	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); NOM (Mexico); UL Listed; cUL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No