

SmartRack Sliding Steel Rack Shelf - 1U, Vented, 28.3 in. Deep, Holds up to 50 lb. (23 kg)

MODEL NUMBER: SRSHELF4PSLVENT











Sliding rack shelf houses a wireless access point or other non-mounted device and saves space in your data center.

Features

1U Vented Sliding Rack Shelf Secures Non-Rack Equipment in Your Data Center

This SmartRack® shelf with sliding side brackets supports monitors, wireless access points, tower units and other IT equipment not typically stored in a rack. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRSHELF4PSLVENT has a maximum load capacity of 50 pounds (22.7 kilograms). The expandable side rails support installation in racks with front-to-rear rail distances between 28 inches (71 centimeters) and 46 inches (117 centimeters).

Maximizes Rack Space and Saves Desk or Floor Space in a Busy Office

The steel shelf mounts easily into 1U of space in a standard 4-post open frame rack or rack enclosure using the included hardware. It is 28.3 inches (72 centimeters) deep for organizing network and other non-rack equipment in your small office or server room. The vented surface allows generous airflow to keep your equipment cool and functioning at its peak.

Highlights

- Universal-mount 1U rack shelf secures non-rack equipment like WAPs and monitors
- Shelf slides in and out of the rack to allow easy access to devices and cabling
- Heavy-duty cold-rolled steel construction with maximum load capacity of 50 lb.
- Vented design maximizes airflow to protect equipment against excessive heat
- Easy to install in a standard 4post rack using the included hardware

Package Includes

- SRSHELF4PSLVENT 1U Sliding Shelf, 28.3 in. Deep (72 cm)
- (8) M6 screws
- (8) M6 cup washers
- (8) M6 cage nuts
- Instruction sheet

Specifications

OVERVIEW		
UPC Code	037332263148	
Product Type	Sliding Shelf	
Device Compatibility	Monitor/HDTV; Network Switch; Router	
Accessory Type	Rack Shelves	
Accessory Class	Rack Accessories	
PHYSICAL		
Color	Black	



Rack Height	1U	
Maximum Device Depth (cm)	116.33	
Maximum Device Depth (in.)	45.8	
Maximum Device Depth (mm)	1,163	
Maximum Weight Capacity (lbs.)	50	
Maximum Weight Capacity (kg)	23	
Minimum Device Depth (cm)	71.88	
Minimum Device Depth (in.)	28.3	
Minimum Device Depth (mm)	719	
Unit Dimensions (hwd / in.)	2.375 x 19.000 x 29.500	
Unit Dimensions (hwd / cm)	4.45 x 48.21 x 76.48	
Unit Weight (lbs.)	18.300	
Unit Weight (kg)	8.30	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; EIA/ECA-310-E	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	5-year limited warranty	



© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.