

## SmartRack 3U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Structured Wiring Enclosure, Adjustable Equipment Brackets

MODEL NUMBER: SRWF6UMOD



Secures and organizes rack equipment, as well as other equipment not typically stored in a rack, such as modems and routers.

### Features

**Rugged 3U Enclosure Ideal for Housing Regular Rack and Non-Rack Network Equipment** This heavy-duty steel enclosure secures and houses both regular rack equipment and other equipment not typically mounted in an EIA-standard 19-inch rack. It is recommended for wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need audio/video, voice and data infrastructure to be secure, organized and out of the way. Constructed with a durable black powder-coated finish, the vertical equipment rack has a maximum load capacity of 150 lbs (68 kgs).

**Connect a Modem, Router and Other Non-Rack Equipment Inside the Enclosure** Two pre-installed, but removable, 1U shelves with adjustable metal equipment brackets attach to the cabinet's square mounting holes. Just place your modem, router, firewall, switch, power block or other non-rack equipment on the brackets, and use the included thumbscrew to secure them to the rack. Four RJ45 jacks are built into the rack cabinet for connecting your devices to a network.

**Low-Profile Design Accommodates Switches, Panels and Other Standard Rack Equipment** Remove the two shelves to reveal two 3U areas for rack-mount equipment, one above the other, forming a total mounting space of 6U. The enclosure extends less than five inches from the wall, while housing equipment up to 16.5 inches deep, including network switches and patch panels.

**Keeps Important Equipment Secure and Easy to Access** The reversible front door locks securely with a built-in combination lock to help prevent damage, tampering or theft. The vented cabinet allows air to flow freely and keep equipment cool. Brush-strip cable plates on both sides allow easy cable routing while preventing dust from entering.

**Easy Enclosure Deployment and Equipment Installation** The structured wiring cabinet comes fully assembled and ready to mount to the wall. The equipment brackets adjust easily and allow for flexibility in storing routers and other devices.

**Meets Payment Card Industry Standards** The SRWF6UMOD provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or transmit credit card information.

### Highlights

- 2 removable 1U shelves with adjustable metal brackets secure non-rack equipment
- Houses 2 areas of 3U of rack equipment up to 16.5 in. deep (when 1U shelves are removed)
- Structured wiring cabinet extends less than 5 in. from wall with max capacity of 150 lbs (68 kgs)
- 4 built-in RJ45 jacks connect installed modem, router and other equipment to network
- Ships fully assembled for immediate installation in back office area or network closet

### Applications

- Simplify the installation and maintenance of multiple network connections by storing equipment together
- Organize various A/V, voice and data network cable runs to cut down on cord clutter
- Protect valuable components from damage, tampering or theft to prevent costly downtime and equipment replacement

### Package Includes

- SRWF6UMOD 3U Structured Wiring Enclosure
- (2) Pre-installed 1U shelves
- Adjustable equipment brackets
- Combination lock instructions

## Specifications

<b>OVERVIEW</b>	
UPC Code	037332250629
Device Compatibility	Patch Panel; Network Switch; Server
Rack Type	Small Enclosure
<b>PHYSICAL</b>	
Color	Black
Rack Height	3U
Rack Depth	Mid; Shallow; Standard
Maximum Device Depth (cm)	41.91
Maximum Device Depth (in.)	16.5
Maximum Device Depth (mm)	419
Shipping Dimensions (hwd / in.)	10.50 x 23.00 x 38.10
Shipping Weight (kg)	16.96
Unit Dimensions (hwd / in.)	35.560 x 20.000 x 7.070
Unit Dimensions (hwd / cm)	90.32 x 50.80 x 17.96
Unit Weight (lbs.)	30.90
Unit Weight (kg)	14.02
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Number of Vertical Mounting Rails	2
<b>FEATURES &amp; SPECIFICATIONS</b>	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.