


Instant-Read AC Outlet Circuit Tester with Diagnostic LEDs

MODEL NUMBER: CT120



Highlights

- Simple to use plug-in tester
- Instantly displays several common wiring fault

Package Includes

NEMA 5-15PCT120 circuit tester
Operating instructions

Description

This instant-read CT120 circuit tester detects wiring stability in standard 120V AC wall sockets. Simply plug the circuit tester into a receptacle and view the lighted three-lamp status display for verification of correct wiring, open ground, open neutral, open hot, hot-ground reversal and hot-neutral reversal fault conditions. Sticker on the tester offers lighting combinations for each wiring condition. Ultra-portable design and easy-to-read lighted display makes the CT120 an excellent addition to any laptop carrying case, tool belt or workbench. Low-cost design saves the expense of hiring an electrician to determine wiring stability.

Features

Offers instant-read notification of correct wiring status of any 120VAC wall socket with a standard NEMA5-15R receptacle (not for use with Ground Fault Interrupt -GFI outlets).

Diagnoses several common wiring faults, including open ground, open neutral, hot-ground reversal and hot-neutral reversal fault conditions (detects most common wiring problems, but not all fault conditions)

Lighted, easy to read 3 lamp status display allows non-technical users to quickly determine the presence of wiring problems and schedule electrical repairs without damage to sensitive electronic devices

Ultra-portable design makes the CT120 and ideal addition to any laptop carrying case, tool belt or workbench

Prevents equipment damage and unsafe wiring by easily identifying common electrical fault conditions so that they can be repaired by a qualified electrician

Low cost design saves the expense of hiring a professional electrician to determine wiring stability

Specifications

OVERVIEW	
UPC Code	037332116345
Accessory Type	Circuit Tester
Accessory Class	Power Inverter Accessories

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED Details	3 indicator lights (2 yellow / 1 red)
PHYSICAL	
Housing Color	Black
Shipping Dimensions (hwd / in.)	4.80 x 1.80 x 4.00
Shipping Dimensions (hwd / cm)	12.19 x 4.57 x 10.16
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	3.000 x 1.500 x 0.500
Unit Dimensions (hwd / cm)	7.62 x 3.81 x 1.27
Unit Weight (lbs.)	0.08
Unit Weight (kg)	0.04
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty