

## 24" CIRCULATION FAN

24CFO-B

### Product Description

Schaefer OSHA compliant circulation fans meet all OSHA safety regulation while delivering maximum airflow. These 2-speed fans have the versatility to be mounted on a ceiling, wall, pedestal or cart, which makes them the ideal cooling solution for any commercial, industrial or agricultural facility.

### Features

Matched direct drive motors and blades for highest achievable levels of airflow, rated up to 12,000 cfm

Powder coated steel guards for corrosion resistant and durability

Energy efficient designed for additional cost savings, draws as little as 1.6 amps

Thermally protected, heavy-duty, maintenance free, 2-speed motors for long life

Two year warranty

Made in the USA



### Specifications

<b>Blade Color</b>	Metallic
<b>Brand</b>	Schaefer
<b>Drive</b>	Direct
<b>Enclosure</b>	TEAO
<b>Frame Size</b>	48YZ
<b>Phase</b>	1
<b>Speeds</b>	2
<b>Vfd Compatible</b>	No
<b>Cfm/watt (free Air)</b>	23.2
<b>Cord</b>	Included - Wired
<b>Diameter (inches)</b>	24
<b>Frequency (hz)</b>	60
<b>Guard Color</b>	Black
<b>Nameplate Amps</b>	2.9/1.6

<b>Number Of Wings</b>	3
<b>Power (hp)</b>	1/4
<b>Product Dimensions (L X W X H Inches)</b>	26.5 x 6.25 x 11.75 in.
<b>Product Net Weight (lbs)</b>	34
<b>Performance Test #</b>	404
<b>Switch</b>	On product
<b>Voltage</b>	115
<b>Maximum Rpm</b>	1100
<b>Blade Material</b>	Aluminum
<b>Cfm (high)</b>	5280
<b>Cfm Calculation Standard</b>	ANSI/AMCA Standard 230-99
<b>Product Color</b>	Black
<b>Product Shipping Dimensions (in)</b>	27 X 27 X 13
<b>Speed Control Compatible?</b>	No

<b>Able To Ship Small Parcel</b>	Yes
<b>Cfm (low)</b>	3850
<b>Cfm Range (free Air)</b>	5001 - 10000
<b>Cord Length (feet)</b>	10
<b>Fixed Or Portable</b>	Fixed
<b>Guard Material</b>	Powder Coated Steel
<b>Mount Type Recommended</b>	WMTA24-B, VS24FMT
<b>Oscillating</b>	No
<b>Country Of Origin</b>	US
<b>Guard Spacing (inches)</b>	1/2 OSHA
<b>Cfm/watt (@0.10")</b>	TBD
<b>Cfm/watt (@0.05")</b>	TBD