

16 1636 05


Power supply connectors




Power supply plug acc. to JEITA RC-5320A JSBP5, straight version, with solder eyes and bend protection

1 of 3 05/2023

1636 05 16





Environmental conditions

Temperature range -20 °C/+70 °C

Materials

PF, HB according to UL94 Insulating body Contact CuZn, nickel-plated

Lötkontakt steel, pre-copper and nickel-plated POM, HB according to UL94

Insulation

Housing PΕ

Mechanical data

Outer diameter 6,5 mm Inner diameter 4,3 mm Diameter center pin 1,4 mm

Connectable conductors for solder area

Cable diameter 4 mm

Electrical data (at Tamb 20 °C)

Rated current 2 A Rated voltage 18 V DC Rated impulse voltage 500 V/60 s Insulation resistance ≥ 100 MΩ

Associated products

Counterparts

☑ 1613 11 **₫** 1614 05

2 of 3 05/2023



16 1636 05

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
1636 05	2	100	500

Packaging:

in bulk, in a cardboard box or a plastic bag

3 of 3 05/2023