

16 1634 01


Power supply connectors





Power supply plug, straight version, with bayonet lock, with solder eyes

1 of 3 05/2023

1634 01 16







Environmental conditions

Temperature range -20 °C/+70 °C

Materials

POM Insulating body

Contact Cu alloy/steel, nickel-plated

ABS Housing

Mechanical data

Outer diameter 5,5 mm Inner diameter 2,5 mm

Connectable conductors for solder area

Cable diameter 5 mm

Electrical data (at Tamb 20 °C)

Rated current 2 A Rated voltage 24 V DC Rated impulse voltage 500 V/60 s Insulation resistance ≥ 100 MΩ

Associated products

Counterparts

☑ 1610 04 **₫** 1613 23

05/2023 2 of 3



16 1634 01

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
1634 01	2	100	500

Packaging:

in bulk, in a cardboard box or a plastic bag

3 of 3 05/2023