



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™

DRIVER-90 HYD W/ISO PUNCH SET



Image
Unavailable

Metric Quick Draw 90 Driver, Slug-Buster ISO Punches and Dies 16.2 mm through 40.5 mm, 2 Draw Studs, 1 Adapter, 1 Spacer and Case

Cat No: 7904-ISO

UPC No: 783310356165

Description

- Compact, lightweight design for portability and fast, easy one-person operation
- Develops 8 tons of hydraulic force for easy punching, even in 10-gauge stainless steel, depending on individual punch capacities
- Quick Draw is perfect for fast, straight-on front panel punching
- Quick Draw 90's right angle driver head rotates over 180 degrees for maximum flexibility in tight working areas
- Quick Draw Flex allows unlimited driver orientation to simplify access to work area
- Can be used with non-round punches within the capacity of the tool (adapter may be required)
- U.S. Patent #6,772,521

Specifications

- Includes : 31971 UPC 31971 Slug-Buster Punch, 32004 UPC 32004 Die, 35162 UPC 35162 ISO-16 Die, 35164 UPC 35164 ISO-25 Die, 35168 UPC 35168 ISO-32 Die, 35159 ISO-40 Die, 33786 UPC 33786 QuickDraw 90 Hydraulic Punch Driver, 1614SS UPC 30043 Draw Stud-3/8 IN x 2-13/16
- Sub Brand : Quick Draw 90
- Type : Hydraulic
- Weight : 12.200 LB (5.500 KG)