

Professionally approved products.

Compression Springs

Steel Compression Spring



[RS Stock No. 751-499](#)

Features:

Ends : Closed
Material : Steel Alloy

Dimensions:

RS Stock No.	Free Length	Outside Diameter	Spring Rate	Minimum Working Length
751499	38.5 mm	5.63 mm	0.7N/mm	16.2 mm
751506	54 mm	6.93 mm	0.63N/mm	17.7 mm
751534	36 mm	5.8 mm	1.8N/mm	21.5 mm
751540	68 mm	8.8 mm	0.44N/mm	23.8 mm
751556	45.5 mm	10.8 mm	0.49N/mm	14.3 mm
751562	34.5 mm	6 mm	4.4N/mm	24.6 mm
751578	30.5 mm	7.3 mm	3.26N/mm	19.9 mm
751584	28.5 mm	9 mm	2.33N/mm	14.3 mm
751590	59 mm	9 mm	1.08N/mm	28.3 mm
751607	26 mm	11 mm	1.85N/mm	11.2 mm
751613	56 mm	11 mm	0.81N/mm	22.4 mm
751629	55.5 mm	13.5 mm	0.61N/mm	19.4 mm
751641	22 mm	9.25 mm	8.92N/mm	10.5 mm
751657	69 mm	9.25 mm	2.69N/mm	30 mm

