




## Han 16B-HTE-NPTF 3/4 Zoll



Part number	09 30 516 0420
Specification	Han 16B-HTE-NPTF 3/4 Zoll
HARTING eCatalogue	<a href="https://b2b.harting.com/09305160420">https://b2b.harting.com/09305160420</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hood
Type	High construction

### Version

Locking type	Double locking lever
Size	16 B
Version	Top entry
Cable entry	1x NPTF 3/4"
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



## Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

## Specifications and approvals

Approvals DNV GL

UL / CSA UL 1977 ECBT2.E235076  
CSA-C22.2 No. 182.3 ECBT8.E235076

CE Yes

## Commercial data

Packaging size 1

Net weight 217 g

Country of origin China

eCl@ss 27440202 Shell for industrial connectors