

D-Sub, MA AWG 18-22 crimp cont



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 000 3576
Specification	D-Sub, MA AWG 18-22 crimp cont
HARTING eCatalogue	https://b2b.harting.com/09670003576

Identification

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts
Performance level	1

Technical characteristics

Conductor cross-section	0.33 ... 0.82 mm ²
Conductor cross-section	AWG 22 ... AWG 18
Contact resistance	≤10 mΩ
Stripping length	4 mm

Material properties

Material (contacts)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a

Commercial data

Packaging size	100
Net weight	0.12 g
Country of origin	Switzerland
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors