

## har-port USB 2.0 A-A; PFT



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1901
Specification	har-port USB 2.0 A-A; PFT
HARTING eCatalogue	<a href="https://b2b.harting.com/09454521901">https://b2b.harting.com/09454521901</a>

### Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 2.0

### Version

Connection type	Type A jack - type A jack
Fixing	Screwable in cover plates

### Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

### Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Silver
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances No

---

## Specifications and approvals

Specifications EN 45545-2

Approvals DNV GL

UL / CSA  
UL 1863 DUXR2.E470046  
CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046

## Commercial data

Packaging size 1

Net weight 13.9 g

Country of origin Germany

European customs tariff number 85389099

eCl@ss 27060304 Appliance cord (data cable)