

Pneumatic contact female 6,0 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6274
Specification	Pneumatic contact female 6,0 mm
HARTING eCatalogue	https://b2b.harting.com/09140006274

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-40 ... +80 °C
Operating pressure	≤8 bar
Tube inner diameter	6 mm

Material properties

Material (contacts)	Delrin acetal
Material (seal)	Buna-N
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	1.16 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27440204 Contact for industrial connectors