

Han 48 HPR Base Panel



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 048 0331
Specification	Han 48 HPR Base Panel
HARTING eCatalogue	https://b2b.harting.com/09400480331

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	for 4 standard inserts - size 16 B

Version

Locking type	Screw locking
Size	48 B
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant



Pushing Performance

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61373 Category 1 Class B
Approvals	DNV GL
CE	Yes

Commercial data

Packaging size	1
Net weight	710.68 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors