

## M23 P ComLock-S Hood 11-17 mm



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 15 600 0483  |
| Specification      | M23 P ComLock-S Hood 11-17 mm   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09156000483">https://b2b.harting.com/09156000483</a> |

### Identification

|                             |                         |
|-----------------------------|-------------------------|
| Category                    | Hoods/Housings          |
| Series                      | Circular connectors M23 |
| Identification              | Power                   |
| Type of hood/housing        | Hood                    |
| Description of hood/housing | EMC version             |

### Version

|              |                             |
|--------------|-----------------------------|
| Locking type | ComLock-S rapid locking     |
| Size         | M23                         |
| Version      | Top entry                   |
| Details      | Compatible to Speedtec (TE) |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C  |
| Degree of protection acc. to IEC 60529 | IP67 / IP69 / IPX9K acc. to ISO 20653 locked condition |
| Clamping range                         | 11 ... 17 mm   |

### Material properties

|                         |                   |
|-------------------------|-------------------|
| Material (hood/housing) | Copper-zinc alloy |
| Surface (hood/housing)  | Nickel plated     |
| RoHS                    | compliant         |
| ELV status              | compliant         |
| China RoHS              | e                 |



Pushing Performance

## Material properties

|                             |    |
|-----------------------------|----|
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances  | No |
| REACH SVHC substances       | No |

## Specifications and approvals

|          |                       |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
|----------|-----------------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 5                                      |
| Net weight                     | 92.2 g                                 |
| Country of origin              | Germany                                |
| European customs tariff number | 85366990                               |
| eCl@ss                         | 27440224 Shell for circular connectors |