

## Han CGM-M M16x1,5 D. 4-8mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5028
Specification	Han CGM-M M16x1,5 D. 4-8mm
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005028">https://b2b.harting.com/19000005028</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-M
Type of accessory	Cable gland

### Technical characteristics

Wrench size	17 19
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M16
Clamping range	4 ... 8 mm
Width across corners	20.8 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	0.019 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)