

## Han CGM-P F+B M25x1,5 D. 11-13 black



Image is for illustration purposes only. Please refer to product description.

Part number	19 15 503 5196
Specification	Han CGM-P F+B M25x1,5 D. 11-13 black
HARTING eCatalogue	<a href="https://b2b.harting.com/19155035196">https://b2b.harting.com/19155035196</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® F+B
Type of accessory	Cable gland

### Version

Pack contents	With spacing washer
---------------	---------------------

### Technical characteristics

Wrench size	32
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP67 / IP69
Size	M25
Clamping range	11 ... 13 mm

### Material properties

Roughness of the surface	≤0.8 µm
Colour (seal)	Blue
Material (cable glands)	Polyamide (PA)
Material (accessories)	VA 1.4305
Colour (accessories)	Black



Pushing Performance

## Specifications and approvals

Approvals	Ecolab Topactive 200
	Ecolab Topactive 500
	Ecolab Topax 66
	Ecolab Topactive OKTO
	Ecolab Topax 990
	FDA 21 CFR 177.1500
	FDA 21 CFR 176.170 (c)
	FDA 21 CFR 177.1390
	FDA 21 CFR 177.1395
	FDA 21 CFR 177.2600

## Commercial data

Packaging size	1
Net weight	31 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27144432 Screwed cable gland (electr.)