This product is not orderable anymore. Please contact your local distribution partner.



HPP V4 C-PFT housing w. clip (NBR)



Part number	09 45 545 0021
Specification	HPP V4 C-PFT housing w. clip (NBR)
HARTING eCatalogue	https://b2b.harting.com/09455450021

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Compact With board locks
	incl. flat seal

Version

Locking type	PushPull	

Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65
	IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained

Product data sheet 09 45 545 0021 HPP V4 C-PFT housing w. clip (NBR)

This product is not orderable anymore. Please contact your local distribution partner.



Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
Specifications	EN 45545-2

Commercial data

Packaging size	100
Net weight	2.98 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140061064
eCl@ss	27440202 Shell for industrial connectors