

M12-PCB-SMT-2PC-4P-ACOD-M-STR(75)



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 311 1416
Specification	M12-PCB-SMT-2PC-4P-ACOD-M-STR(75)
HARTING eCatalogue	https://b2b.harting.com/21033111416

Identification

Category	Connectors
Series	Circular connectors M12
Element	PCB adapter
Specification	Straight

Version

Termination method	Reflow soldering termination (SMT)
Gender	Male
Shielding	Unshielded
Number of contacts	4
Coding	A-coding
Details	Order housings separately
Pack contents	75 pieces on reel

Technical characteristics

Rated current	4 A
Rated voltage	250 V
Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Ambient temperature	-40 ... +85 °C
Mating cycles	≥ 100



Pushing Performance

Technical characteristics

Isolation group	I ($600 \leq CTI$)
-----------------	----------------------

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

Commercial data

Packaging size	1
Net weight	722 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)