

## Han CGM-M M16x1,5 D. 2-6mm



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 19 00 000 5029                                                                        |
| Specification      | Han CGM-M M16x1,5 D. 2-6mm                                                            |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19000005029">https://b2b.harting.com/19000005029</a> |

### Identification

|                          |             |
|--------------------------|-------------|
| Category                 | Accessories |
| Series of hoods/housings | Han® CGM-M  |
| Type of accessory        | Cable gland |

### Technical characteristics

|                                        |                                        |
|----------------------------------------|----------------------------------------|
| Wrench size                            | 17<br>19                               |
| Limiting temperature                   | -40 ... +100 °C                        |
| Degree of protection acc. to IEC 60529 | IP68<br>IP69 / IPX9K acc. to ISO 20653 |
| Size                                   | M16                                    |
| Clamping range                         | 2 ... 6 mm                             |
| Width across corners                   | 20.8 mm                                |

### Material properties

|                             |                                                        |
|-----------------------------|--------------------------------------------------------|
| Material (seal)             | NBR                                                    |
| Material (cable glands)     | Brass                                                  |
| Material (clamping ring)    | Polyamide (PA)                                         |
| Surface (accessories)       | Nickel plated                                          |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50                                                     |
| REACH Annex XVII substances | No                                                     |



Pushing Performance

## Material properties

|                            |      |
|----------------------------|------|
| REACH ANNEX XIV substances | No   |
| REACH SVHC substances      | Yes  |
| REACH SVHC substances      | Lead |

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

## Commercial data

|                                |                                        |
|--------------------------------|----------------------------------------|
| Packaging size                 | 10                                     |
| Net weight                     | 0.019 g                                |
| Country of origin              | Germany                                |
| European customs tariff number | 84849000                               |
| eCl@ss                         | 27144432 Screwed cable gland (electr.) |