

Han 6M Base Surface LC 1 Lever 2 x M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 37 006 1290
Specification	Han 6M Base Surface LC 1 Lever 2 x M20
HARTING eCatalogue	https://b2b.harting.com/19370061290

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Surface mounted housing
Type	Low construction

Version

Locking type	Single locking lever
Size	6 B
Version	Side entry
Cable entry	2x M20
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM



Pushing Performance

Material properties

Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

Commercial data

Packaging size	1
Net weight	196.8 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors