


SEK CAB FLAT STD HF AWG28/7 28P 30,48m



Part number	09 18 028 7001 900
Specification	SEK CAB FLAT STD HF AWG28/7 28P 30,48m
HARTING eCatalogue	https://b2b.harting.com/09180287001900

Image is for illustration purposes only. Please refer to product description.

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)

Version

Cable length	30.48 m
Number of cores	28
Core structure	AWG 28/7

Technical characteristics

Impedance	110 Ω
Limiting temperature	-40 +105 °C unmoved
	-20 +105 °C moved

Material properties

Material (cable)	Non-halogenated
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Material properties

Specifications and approvals

Specifications	UL 1581 UL 758 Style 21151
CE	Yes

Commercial data

Packaging size	1
Net weight	1,650 g
Country of origin	USA
European customs tariff number	85444993
eCl@ss	27061801 Data and communication cable (copper)