

Han E Male Contact CuNi 0.14-0.37 mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6163
Specification	Han E Male Contact CuNi 0.14-0.37 mm ²
HARTING eCatalogue	https://b2b.harting.com/09330006163

Identification

Category	Contacts
Series	Han E [®]
Type of contact	Crimp contact

Version

Gender	Male
Contact identification	acc. to IEC 60584 type J
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm ²
Conductor cross-section	AWG 26 ... AWG 22
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	25
Net weight	1.5 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors