

## Han® S-200A FC CRT 50mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 6264
Specification	Han® S-200A FC CRT 50mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09930006264">https://b2b.harting.com/09930006264</a>

### Identification

Category	Contacts
Series	Han® S
Type of contact	Crimp contact
Description of the contact	Female contact incl. rubber sleeve

### Version

Manufacturing process	Turned contacts
-----------------------	-----------------

### Technical characteristics

Conductor cross-section	50 mm <sup>2</sup>
Conductor cross-section	AWG 1/0
Operating current	≤200 A
Contact resistance	≤0.3 mΩ
Stripping length	22 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (accessories)	Thermoplastic polyurethane (TPU)



Pushing Performance

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	1
Net weight	47.13 g
Country of origin	China
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors