

M23 HBM front 2,7mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 100 0301
Specification	M23 HBM front 2,7mm
HARTING eCatalogue	https://b2b.harting.com/09151000301

Identification

Category	Hoods/Housings
Series	Circular connectors M23
Identification	Signal
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Front mounting

Version

Locking type	Screw locking ComLock rapid locking
Size	M23
Fixing	Fixing hole 4x 2.7 mm

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	19.3 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440224 Shell for circular connectors