



Pushing Performance

Han 24EMC/B-HTE-3xM25 (HT)



Part number	19 62 824 0476
Specification	Han 24EMC/B-HTE-3xM25 (HT)
HARTING eCatalogue	https://b2b.harting.com/19628240476

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] EMC/B Han [®] High Temp
Type of hood/housing	Hood
Type	High construction

Version

Locking type	Double locking lever
Size	24 B
Version	Top entry
Cable entry	3x M25

Technical characteristics

Limiting temperature	-40 ... +125 °C -40 ... +200 °C With Han [®] High Temp components
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

Commercial data

Packaging size	1
Net weight	245 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors