

## Han 24Ex UL-HTE-M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 36 524 1422
Specification	Han 24Ex UL-HTE-M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19365241422">https://b2b.harting.com/19365241422</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> Ex
Type of hood/housing	Hood

### Version

Locking type	Double locking lever
Size	24 B
Version	Top entry
Cable entry	1x M32
Field of application	Connectors for explosion hazardous environments
Details	for US purposes only
Details	ATTENTION! Only to be used with Han <sup>®</sup> Ex inserts!

### Technical characteristics

Limiting temperature	-20 ... +40 °C
Degree of protection acc. to IEC 60529	IP65 With cable gland

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
RoHS	compliant
ELV status	compliant



Pushing Performance

## Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Commercial data

Packaging size	1
Net weight	496 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors