

Han CGM-M-Rail M25 D.14.5-18mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 7123
Specification	Han CGM-M-Rail M25 D.14.5-18mm
HARTING eCatalogue	https://b2b.harting.com/19000007123

Identification

Category	Accessories
Series of hoods/housings	Han [®] CGM-M-Rail
Type of accessory	Cable gland
Description of the accessory	Railway version

Technical characteristics

Tightening torque	≤7 Nm (depending on the cable and the seal insert used)
Wrench size	27 30
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68
Size	M25
Clamping range	14.5 ... 18 mm
Width across corners	32.9 mm

Material properties

Material (seal)	EPDM
Material (cable glands)	Brass
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

Material properties

REACH Annex XVII substances	No
-----------------------------	----

REACH ANNEX XIV substances	No
----------------------------	----

REACH SVHC substances	Yes
-----------------------	-----

REACH SVHC substances	Lead
-----------------------	------

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
----------------	----

Net weight	0.1 g
------------	-------

Country of origin	Germany
-------------------	---------

European customs tariff number	84849000
--------------------------------	----------

eCl@ss	27144432 Screwed cable gland (electr.)
--------	--