

M23 P Cable to Cable Housing 11-17mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 600 0311
Specification	M23 P Cable to Cable Housing 11-17mm
HARTING eCatalogue	https://b2b.harting.com/09156000311

Identification

Category	Hoods/Housings
Series	Circular connectors M23
Identification	Power
Type of hood/housing	Panel feed through housing
Description of hood/housing	Rear mounting EMC version

Version

Locking type	Screw locking ComLock rapid locking
Size	M23

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 locked condition
Clamping range	11 ... 17 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	80.5 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440224 Shell for circular connectors