

Han 3A Thermopl. Cover, Sealing for Base



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5445
Specification	Han 3A Thermopl. Cover, Sealing for Base
HARTING eCatalogue	https://b2b.harting.com/09200035445

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings
	for surface mounted housings
	Thermoplastic
	With seal
	With fixing cord

Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for mounted female insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Polycarbonate (PC)
-------------------------	--------------------



Pushing Performance

Material properties

Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	5.72 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440208 Cap for industrial connectors