

Han 16B-HMC-gg-R-M32



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 30 216 1442 |
| Specification | Han 16B-HMC-gg-R-M32 |
| HARTING eCatalogue | https://b2b.harting.com/19302161442 |

Identification

| | |
|--------------------------|----------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] HMC |
| Type of hood/housing | Hood |
| Type | Low construction |

Version

| | |
|----------------------|---|
| Locking type | Single locking lever |
| Size | 16 B |
| Version | Top entry |
| Cable entry | 1x M32 |
| Field of application | Special hoods and housings for high mating cycles |

Technical characteristics

| | |
|---|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Mating cycles with other HMC components | ≥10,000 |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 |
| | 4X |
| | 12 |

Material properties

| | |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |



Pushing Performance

Material properties

| | |
|-----------------------------|-----------|
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 143.8 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27440202 Shell for industrial connectors |