

Han® S-200A FC CRT 25mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 6262
Specification	Han® S-200A FC CRT 25mm ²
HARTING eCatalogue	https://b2b.harting.com/09930006262

Identification

Category	Contacts
Series	Han® S
Type of contact	Crimp contact
Description of the contact	Female contact incl. rubber sleeve

Version

Manufacturing process	Turned contacts
-----------------------	-----------------

Technical characteristics

Conductor cross-section	25 mm ²
Conductor cross-section	AWG 4
Operating current	≤200 A
Contact resistance	≤0.3 mΩ
Stripping length	22 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (accessories)	Thermoplastic polyurethane (TPU)
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	1
Net weight	42.37 g
Country of origin	China
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors