

## Han Snap Plastic Housing Size 10B



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 010 0401
Specification	Han Snap Plastic Housing Size 10B
HARTING eCatalogue	<a href="https://b2b.harting.com/09330100401">https://b2b.harting.com/09330100401</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Snap®
Type of hood/housing	Shell housing

### Version

Locking type	Snap-in latches
Size	10 B
Version	Top/side entry
Pack contents	2 half shells with blind plugs

### Technical characteristics

Tightening torque	0.8 Nm
Limiting temperature	-40 ... +125 °C
Retention force	≥300 N locked condition

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

## Specifications and approvals

Specifications IEC 60068-2-6 Vibration (sinusoidal)  
IEC 60068-2-27 Shock

## Commercial data

Packaging size 1

Net weight 30 g

Country of origin Germany

European customs tariff number 85389099

eCl@ss 27440202 Shell for industrial connectors