

M12-PCB-SMT-2PC-4P-DCOD-F-STR-SHLD(75)



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 381 2405
Specification	M12-PCB-SMT-2PC-4P-DCOD-F-STR-SHLD(75)
HARTING eCatalogue	https://b2b.harting.com/21033812405

Identification

Category	Connectors
Series	Circular connectors M12
Element	PCB adapter
Specification	Straight

Version

Termination method	Reflow soldering termination (SMT)
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Details	Order housings separately
Pack contents	75 pieces on reel

Technical characteristics

Rated current	4 A
Rated voltage	250 V
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Insulation resistance	$>10^8 \Omega$
Ambient temperature	-40 ... +85 °C
Mating cycles	≥ 100



Pushing Performance

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

Commercial data

Packaging size	1
Net weight	727 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)