

## Han D F Crimp Contact 0,75mm<sup>2</sup> Au



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 6225
Specification	Han D F Crimp Contact 0,75mm <sup>2</sup> Au
HARTING eCatalogue	<a href="https://b2b.harting.com/09150006225">https://b2b.harting.com/09150006225</a>

### Identification

Category	Contacts
Series	Han D <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.75 mm <sup>2</sup>
Conductor cross-section	AWG 18
Operating current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	8 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

## Commercial data

Packaging size	100
Net weight	0.65 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors