

M23 Hood 11-17 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 100 0403
Specification	M23 Hood 11-17 mm
HARTING eCatalogue	https://b2b.harting.com/09151000403

Identification

Category	Hoods/Housings
Series	Circular connectors M23
Identification	Signal
Type of hood/housing	Hood
Description of hood/housing	EMC version

Version

Locking type	Screw locking
Size	M23
Version	Top entry

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition
Clamping range	11 ... 17 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	76 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440224 Shell for circular connectors